

DIMENSIONAL SPECIFICATIONS

Overall Dimensions:

Nominal Dimension: 72" x 24" x 29" (W-D- H)

Actual Dimension: 71-15/16" x 23-7/8" x 28-7/8" (W-D- H)

Drawer (Inside Dimensions):

Lateral File: 31-13/16" x 17-1/4" x 8-15/16" (W-D-H)

Knee Space Between Pedestals:

34-3/4" x 19-9/16" x 28-9/32" (W-D-H)

MATERIAL SPECIFICATIONS

Top:

- 1-1/8" thick particleboard with Kraft backer and high-pressure laminate top cover
- Top dimensions – 69-13/16" x 23-7/8"(W-D)

End Panels:

- 1-1/8" particleboard cores with melamine back, high-pressure laminate (HPL) top cover, and .8mm edge trim on bottom.
- End panel dimensions –23-7/8"x 28-1/8" (W-H)

Skirt:

- 3/4" particleboard with melamine both front and back.
- Skirt dimensions- 69-19/32"x 28-7/32" (W-H)

Lateral Drawer Material:

- **FRONT**-3/4"thick particleboard with melamine both front and back .5mm edgebanding on both sides, access pull on either top or bottom, and opposite side .5 mm banding, 33-7/16" x 12-1/16 (W-H)
- **SIDES**-7/16"thick fiberboard, 9-1/2" high.
- **BACK**-7/16"thick fiberboard, 9-1/2" high.
- **BOTTOM**-3/16"thick printed hardboard.
- **CONSTRUCTION**-Sides mortise/tenon into drawer front, stapled to back and subfront at corners. Bottom fits into slots on sides.



10700 Series H10748L Technical Specifications

Grommet:

- There are two grommets that are located in the back corners of the desk. They are rectangle in shape. They are 1-7/8" from either side of the desk and 16-7/8" from the front edge of the desk.
- Size: 3-1/4" x 1-7/8" (W-H)

Hardware:

Product Pack-262-3137

Hangrail Pack-262-4110

MODEL FEATURES

- .625 Radius edge on 107 tops
- 3-1/2" Approach Side Top Overhang
- 3/4" Adjustable Glides
- **Lateral file:** Has mechanical interlock to prevent extension of two drawers at one time.
- **Interlock Assy** #- 224-5000
- **10500** Series wood produce meets or exceeds **ISTA** shipping and **ANSI/BIFMA X5.5** (latest Rev.) testing requirements for office furniture.

PARTICLEBOARD: All particleboard is ANSI grade IM3 or better.

CARTONING INFORMATION

Carton-Outside Dimensions: 74-11/32" x 26-11/32" x 31-27/32" (W-D-H)

Cubes: 36.2

Carton #: 242-3056

Weight: 247lbs