

DIMENSIONAL SPECIFICATIONS

Overall Dimensions:

Nominal Dimension: 66" x 30" x 29-1/2" (W-D-H)

Actual Dimension: 65-15/16" x 29-7/8" x 29-7/8" (W-D-H)

Pedestals (Outside Dimensions with Drawer Front):

Letter Width Desk: 14-7/8" x 24-1/2" x 17-3/4" (W-D-H)

Drawer (Inside Dimensions):

Letter Width Desk Box: 12-1/4" x 19-13/16" x 4-1/16" (W-D-H)

Letter Width Desk File: 12-1/4" x 19-13/16" x 10-1/2" (W-D-H)

Knee Space Between Pedestals:

48-43/64" x 24-39/64" x 28-7/32" (W-D-H)

MATERIAL SPECIFICATIONS

Top:

- 1-1/8" thick particleboard with Kraft Backer surface bottom and high-pressure laminate (HPL) top cover.
- Top dimensions – 65-15/16" x 29-7/8" (W-D)
- Top end caps: solid hardwood

End Panels:

- 1-1/8" particleboard cores with melamine back, a high-pressure laminate (HPL) top cover, and .8mm edge trim on the bottom.
- End panel dimensions – 29-7/8" x 28-1/8" (W-H)

Full Height Skirt:

- 3/4" particleboard with melamine both front and back, and .5 mm edgebanding on side.
- Skirt dimensions – 63 19/32" x 28-7/32" (W-H)

Inside Panel:

- 3/4" particleboard with melamine both front and back.

Box Drawer Material:

- **FRONTS**-3/4" thick particleboard with melamine both front and back .5mm edgebanding on both sides and top.
- **SIDES**-7/16" thick fiberboard, 3-5/8" high.
- **BACK**-7/16" thick fiberboard, 3-5/8" high.
- **BOTTOM**-3/16" thick printed hardboard.
- **SUBFRONT**-7/16" thick fiberboard, 3-5/8" high.
- **CONSTRUCTION**-Sides mortise/tenon into drawer front, stapled to back and subfront at corners. Bottom fits into slots on sides.

File Drawer Material:

- **FRONTS**-3/4" thick particleboard with melamine both front and back .5mm edgebanding on both sides and top.
- **SIDES**-7/16" thick fiberboard, 9-1/2" high.
- **BACK**-7/16" thick fiberboard, 9-1/2" high.
- **BOTTOM**-3/16" thick printed hardboard.
- **SUBFRONT**-7/16" thick fiberboard, 9-1/2" high.
- **CONSTRUCTION**-Sides mortise/tenon into drawer front, stapled to back and subfront at corners. Bottom fits into slots on sides.

Grommet:

- There are two grommets in the top. They are located 22-7/32" back from the front edge of the desk. One is 1-7/8" from the left edge, and the other is the same distance from the right side.
- Size: 3-1/4" x 1-7/8" (W-H)

Hardware:

Frame Pack-242-6769

Divider Pack-262-4002

Hangrail Pack-262-4107

Product Pack-262-3130

MODEL FEATURES

- 4-1/2" Approach Side Top Overhang
- 3/4" Adjustable Glides
- 3/4" Extension Ball Bearing Box Drawer Slide
- Full Extension ball Bearing File Drawer Slide
- **File Drawer**: Letter and legal width side-to-side filing, letter width front to back filing. Hangrails are provided for all file drawers. Use Hanging folders with a maximum height of 9-3/4".

The HON Company
200 Oak Street
Muscatine, IA 52761
800-833-3964
hon.com



10700 Series H10783R Technical Specifications

- **Lock #:** 50-5575
- **10700** Series wood produce meets or exceeds **ISTA** shipping and **ANSI/BIFMA X5.5** (latest Rev.) testing requirements for office furniture.
- *** Classical contemporary styling with hard wood accents

PARTICLEBOARD: All particleboard is ANSI grade IM3 or better.

CARTONING INFORMATION

Carton-Outside Dimensions: 68-3/8" x 32-3/8" x 32" (W-H-D)

Cubes: 41.0

Carton #: 242-3052

Weight: 229 lbs

REVISIONS

1.1-Corrected carton size and cube. (1-19-04)