

# NRG® 300 Series

## Perimeter Wallpack

- Full polycarbonate front provides vandal resistance and efficient spread; Lateral coverage on HID units is 5 times the typical mounting height up to 10 feet; Internally painted bronze finish for lasting appearance; Fluorescent photocontrol version available in white
- New 56 LED units provide long-life with low energy consumption, a perfect upgrade for older units
- Motion controlled unit has 180° detection range – saves energy by providing illumination only when needed, 42w CFL version only
- Lamp included with all versions
- Rugged cast aluminum back housing for rigid mounting; Bottom 1/2" conduit knockout for surface conduit wiring (except on 'MS' unit); Back hub allows access to recessed wiring boxes; Two point mounting
- LED/HID 120V-277V button photocontrol
- CFL 120V button photocontrol only
- Listed to UL 1598 for use in wet locations
- Tamper resistant center pin Torx hardware included



WALLPACKS

### ORDERING INFORMATION

Catalog Number <sup>1</sup>		Wattage	Voltage	Color	Weight lbs. (kg)
Without Photocontrol	With Photocontrol				
<b>High Pressure Sodium</b>					
<b>NRG-301B</b>	<b>NRG-301B-PC<sup>2,3</sup></b>	50w	120V	Bronze	5 (2.3)
<b>NRG-307B</b>	<b>NRG-307B-PC<sup>2,3</sup></b>	70w	120V	Bronze	5 (2.3)
<b>Pulse Start Metal Halide</b>					
<b>NRG-350B</b>	<b>NRG-350B-PC<sup>2,3</sup></b>	50w	120V	Bronze	6.5 (2.9)
<b>Electronic Fluorescent<sup>4</sup></b>					
–	<b>NRG-306B-PC<sup>2</sup></b>	26w	120-277V (-PC120)	Bronze	4.2 (1.9)
–	<b>NRG-304B-PCW<sup>2</sup></b>	42w	120-277V (-PC120)	White	4.2 (1.9)
<b>NRG-304B</b>	<b>NRG-304B-PC<sup>2</sup></b>	42w	120-277V (-PC120)	Bronze	4.2 (1.9)
<b>Motion Controlled Electronic Fluorescent<sup>4</sup></b>					
–	<b>NRG-304B-MS<sup>5</sup></b>	42w	120V	Bronze	6 (2.7)
<b>56 LED – 1513/1532 Lumens – 4000K/5000K – 80 CRI</b>					
<b>NRG-356L-4K-U<sup>6</sup></b>	<b>NRG-356L-4K-U-PC<sup>6</sup></b>	20w	120-277V	Bronze	6 (2.7)
<b>NRG-356L-5K-U<sup>6</sup></b>	<b>NRG-356L-5K-U-PC<sup>6</sup></b>	20w	120-277V	Bronze	6 (2.7)

- 1 Lamp included
- 2 120V only when ordered with photocontrol
- 3 120V NPF ballast for HID
- 4 CFL lamps are 4-Pin, 3500K, GX24q-4
- 5 Motion sensor has 180° detection range, adjustable time-on and sensitivity settings
- 6 LED units feature five year limited warranty

### ACCESSORIES - Order Separately

Catalog Number	Description
<b>PBT-1</b>	Button photocontrol, 120V
<b>PBT-234</b>	Button photocontrol, 208, 240, 277V

### REPLACEMENT PART

Catalog Number	Description
<b>SM352-COVER</b>	Polycarbonate front cover, Bronze

