

### DIMENSIONAL SPECIFICATIONS

---

#### Overall Dimensions:

Nominal Dimension: 72" x 30" x 29-1/2" (W-D-H)

Actual Dimension: 71-15/16" x 29-7/8" x 29-7/8" (W-D-H)

#### Pedestals (Outside Dimensions with Drawer Front):

Letter Width Desk: 14-7/8" x 24-1/2" x 17-3/4" (W-D-H)

#### Drawer (Inside Dimensions):

Letter Width Desk Box: 12-1/4" x 19-13/16" x 4-1/16" (W-D-H)

Letter Width Desk File: 12-1/4" x 19-13/16" x 10-1/2" (W-D-H)

#### Knee Space Between Pedestals:

39-3/4" x 24-39/64" x 28-7/32" (W-D-H)

### MATERIAL SPECIFICATIONS

---

#### Top:

- 1-1/8" thick particleboard with melamine surface top and bottom, 2mm PVC edgebanding around all four edges.
- Top dimensions – 71-15/16" x 29-7/8" (W-D)

#### End Panels:

- 1-1/8" particleboard cores with melamine both front and back, .5mm PVC edgebanding the two side edges and .8mm (edge trim on bottom).
- End panel dimensions – 29-7/8" x 28-1/8" (W-H)

#### Full Height Skirt:

- 3/4" particleboard with melamine both front and back, and .5 mm edgebanding on side.
- Skirt dimensions – 69-19/32" x 28-7/32" (W-H)

#### Inside Panel:

- 3/4" particleboard with melamine both front and back.



## 10500 Series Model H10593 Technical Specifications

### Box Drawer Material:

- **FRONTS**-3/4" thick particleboard with melamine both front and back .5mm PVC edgbanding on both sides and top.
- **SIDES**-7/16" thick fiberboard, 3-5/8" high.
- **BACK**-7/16" thick fiberboard, 3-5/8" high.
- **BOTTOM**-3/16" thick printed hardboard.
- **SUBFRONT**-7/16" thick fiberboard, 3-5/8" high.
- **CONSTRUCTION**-Sides mortise/tenon into drawer front, stapled to back and subfront at corners. Bottom fits into slots on sides.

### FILE DRAWER MATERIAL:

- **FRONTS**-3/4" thick particleboard with melamine both front and back .5mm edgbanding on both sides and top.
- **SIDES**-7/16" thick fiberboard, 9-1/2" high.
- **BACK**-7/16" thick fiberboard, 9-1/2" high.
- **BOTTOM**-3/16" thick printed hardboard.
- **SUBFRONT**-7/16" thick fiberboard, 9-1/2" high.
- **CONSTRUCTION**-Sides mortise/tenon into drawer front, stapled to back and subfront at corners. Bottom fits into slots on sides.

### Hardware:

*Hangrail Pack- 262-4107*

*Product Pack- 262-3129*

## MODEL FEATURES

---

- 10-1/2" Approach Side Top Overhang
- 3/4" Adjustable Glides
- 3/4" Extension Ball Bearing Box Drawer Slide
- Full Extension ball Bearing File Drawer Slide
- **File Drawer:** Letter and legal width side to side filing, letter width front to back filing. Hangrails are provided for all file drawers. Use Hanging folders with a maximum height of 9-3/4".
- **Lock #:** 50-5575
- **10500** Series wood produce meets or exceeds **ISTA** shipping and **ANSI/BIFMA X5.5** (latest Rev.) testing requirements for office furniture.

**PARTICLEBOARD: All particleboard is ANSI grade IM3 or better.**



## CARTONING INFORMATION

---

## 10500 Series Model H10593 Technical Specifications

**Carton-Outside Dimensions:** 74-3/8" x 38-3/8" x 32" (W-H-D)

**Cubes:** 52.9

**Carton #:** 242-5710

**Weight:** 340lbs

## REVISIONS

---

**1.1-Corrected cartons size and cube. (1-19-04)**