



SPECIFICATION

Part Numbers: KSW26Color-0100/1000 ROLLS
For Cut/Strip/Wrap Applications

This specification is for wire per UL Style 1422, 105°C, no voltage rated, 26 AWG. Solid silver plated oxygen free copper.

CONDUCTOR:

Size: 26 AWG. Solid
Circular Mil Area: 246 Minimum
Material: Silver plated oxygen free, high Conductivity copper per ASTM-B170
DC Resistance.: @20°C(68°F) max. 43.53 Ω/M'

Elongation: 20% before insulation
Plating: Silver, 40 micro-inch minimum per ASTM-B 298.
Weight: 0.765 lbs/M'
Diameter: 0.0159" nom.
0.0158" min.

INSULATION:

Material: Kynar 460
Diameter: 0.0275" ± .0015"
Min. Avg. Wall: 0.005"
Min. any. Pt.: 0.004"
Spark Test: 2,000 VAC RMS
Color: As specified
Weight: 0.285 lbs/M'
Total Weight: 1.05 lbs/M'
Flammability VW-1

Material is further processed in proprietary operations so as to be suitable for cut, strip and wrap applications

M' = 1000 Feet