

TYPE SL



This non-UL, extra-flexible product, available in the smaller diameters, is designed for tight-spot installation and where continuous flexing is required of a steel-wound hose.

CONSTRUCTION:

Type SL is helically wound from a strip of electro-galvanized steel. It is sized to be used with a variety of set-screw and clamp type connectors.

APPLICATION:


Offers good mechanical protection to wiring in a variety of OEM applications.

RoHS and WEEE Compliant.

METAL USED: Steel



Squarelock



Trade Size		Type	Diameter (In.)		Min Inside Radius (In.)	Weight (Lbs.)/100 Ft.	Coil Footage (Ft.)	
U.S.	Metric		Inner Min/Max	Outer Min/Max			Length	Part #
-	-	SL-316	0.172/0.202	0.280/0.310	0.75	5	250	91202
-	-	SL-140	0.235/0.265	0.328/0.358	0.75	6	250	92202
5/16	-	SL-516	0.297/0.327	0.391/0.421	0.75	7	250	93202
-	-	SL-380	0.360/0.390	0.485/0.515	1.00	8	250	94202
-	-	SL-716	0.422/0.452	0.547/0.577	1.00	9	250	95202
3/8	16mm	SL-10	0.492/0.512	0.617/0.637	1.00	10	250	96202
-	-	SL-916	0.547/0.577	0.672/0.702	1.25	12	150	99206
1/2	-	SL-11	0.622/0.642	0.747/0.767	1.50	15	150	97202
-	20mm	SL-11M	0.650/0.670	0.775/0.795	1.50	15	150	972021
-	-	SL-340	0.735/0.765	0.865/0.895	1.50	17	150	98202
3/4	25mm	SL-12	0.827/0.847	0.957/0.977	2.00	18	100	98222
1	-	SL-13	1.041/1.066	1.191/1.216	2.00	27	50	98232
-	32mm	SL-13M	1.102/1.122	1.252/1.272	2.00	27	50	982321