

TYPE USL



This extra-flexible steel conduit is recognized by UL and CSA for use within listed and certified assemblies.

CONSTRUCTION:

Helically formed from hot-dipped galvanized steel, Type USL offers good corrosion resistance and provides excellent mechanical protection to enclosed circuits. It is sized to be used with a variety of set-screw and clamp type connectors.

APPLICATION:


This product is intended as a factory-installed component of various assemblies. Typical uses include: modular office partitions, showcase lighting and range tops. For component applications within Canada, ask for **CSA Report #LO 4000-4875**.

UL Recognized File #E53253

RoHS and WEEE Compliant.

METAL USED: Steel

Squarelock—Type USL



TYPE UG



A fully-interlocked, non-UL flexible steel conduit designed for high strength in “tight-spot” installations.

CONSTRUCTION:

This conduit is manufactured from a bright tin-plated steel strip that is fully interlocked at the edges, to produce a strong yet flexible product. The interlock feature does not allow the conduit to unravel if twisted, and permits the conduit to retain its shape when bent. This lightweight product is compatible with many set-screw and clamp type connectors.


APPLICATION:

The bright appearance of the finished product lends itself to installations where the conduit may be visible after the final assembly.

RoHS and WEEE Compliant.

METAL USED: Steel

Interlock



Trade Size (In.)	Type	Diameter (In.)		Min Inside Radius (In.)	Weight (Lbs.)/100 Ft.	Coil Footage (Ft.)	
		Inner Min/Max	Outer Min/Max			Length	Part #
USL							
-	USL-516	0.297/0.327	0.457/0.487	1-1/4	12	250	91402
-	USL-380	0.360/0.390	0.520/0.550	1-1/4	15	250	92402
-	USL-716	0.422/0.452	0.582/0.612	1-1/2	17	250	93402
3/8	USL-120	0.485/0.515	0.645/0.675	1-1/2	19	250	94402
-	USL-916	0.557/0.577	0.707/0.737	1-1/2	20	250	95402
1/2	USL-580	0.622/0.642	0.732/0.765	2	24	100	96402
3/4	USL-340	0.820/0.840	0.930/0.960	2	32	100	97402
UG							
-	UG-380	0.443/0.473	0.563/0.593	2.5	16	50	91101
-	UG-120	0.755/0.785	0.875/0.905	3.0	22	50	92101
-	UG-340	0.943/0.973	1.063/1.093	3.5	26	50	93101
-	UG-100	1.208/1.238	1.328/1.358	4.5	34	50	94101
-	UG-125	1.485/1.515	1.578/1.608	5.5	50	50	95101
-	UG-150	1.735/1.765	1.843/1.873	6.5	56	50	96101
-	UG-200	2.235/2.265	2.390/2.420	8.5	80	50	97101
-	UG-250	2.735/2.765	2.937/2.967	10.5	85	50	98101
-	UG-300	3.360/3.390	3.438/3.468	13.0	105	50	99101

Note: Electrical trade sizes do not apply to Type UG.