

2' FIBERGLASS PLATFORM LADDER

300 lbs.

TYPE IA LOAD CAPACITY

includes weight
of user plus materials

TOP RAIL GUARD

SLIM, GAPLESS
SLIP-RESISTANT
PLATFORM

DOUBLE-RIVET
STEP
CONSTRUCTION

SHOX™ —
SUPERIOR IMPACT
ABSORPTION

DA BOOT™ —
PATENT
#7,000,731 B2



SHOX



OSHA
REQUIREMENTS

ANSI
American National Standards Institute
of International Standards
ANSI A14.5



LOUISVILLE
LADDER

1-800-666-2811
www.LOUISVILLELADDER.com

MODEL	HT. to PLATFORM	STEP DEPTH	BOTTOM WIDTH	APPROX. SPREAD	APPROX. WT. (LBS)	APPROX. CUBES
FP1502	1' 11"	3"	21 7/8"	28 11/16"	16	4'
FP1503	2' 10"	3"	23 5/16"	34 1/4"	20	5.2'
FP1504	3' 9"	3"	24 13/16"	39 7/8"	22	6.6'
FP1505	4' 9"	3"	26 3/16"	45 3/4"	25	8.1'
FP1506	5' 8"	3"	27 3/4"	52"	28	9.8'
FP1508	7' 7"	3"	30 7/8"	63 3/4"	36	13.6'
FP1510	9' 6"	3"	33 13/16"	75 9/16"	42	17.8'
FP1512	11' 5"	3"	36 13/16"	86 5/8"	64	22.6'

