

METAL FINDER

MetalliScanner® MT 6



Electronic Metal Locator

Locate embedded metal before your drill bit or saw blade does. This powerful dedicated metal scanning tool can locate metal up to 6 inches deep in solid concrete.

MetalliScanner® MT 6 locates both ferrous and non-ferrous metal up to 6 inches (152 mm) deep in concrete and other non-metallic surfaces. It also differentiates between ferrous and non-ferrous metal targets and indicates the target depth in inches and centimeters.

MT 6 indicates when you are approaching a metal object with a large plus (+) sign on the display. When the plus becomes a minus (-), you have crossed over the target and are now moving away.

Use MetalliScanner® MT 6 to find or avoid rebar, cables, pipe, nails in reclaimed wood, nails/tacks in studs behind lath & plaster walls, electrical boxes and conduit, and more.

MetalliScanner® MT 6 is the tool recommended by the My Safe Florida Home Program to assist in hurricane loss mitigation.

- Automatically differentiates between magnetic metal (such as rebar) and non-magnetic metal (such as copper pipe)
- Shows the depth of metal from the surface in both inches and centimeters
- Easy-to-read LCD screen pinpoints the location of metal objects to the nearest ½ inch (13 mm) and depth to the nearest inch (25 mm)
- Helps map out the grid of metal through any nonmetallic construction material, including concrete, tile, and marble



Scan for Metal

SPECIFICATIONS

Dimensions	8.87 in. H x 3.84 in. W x 2.23 in. D (225 mm x 98 mm x 57 mm)
Weight	10.1 oz. (286 g) without battery
Battery Type	9-V alkaline (not included)
Position Accuracy	Center of #4 (½ in.) rebar or ½ in. (13 mm) copper pipe at a minimum grid spacing of 6 in. (152 mm) typically within ½ in. (13 mm)
Depth	Up to 6 in. (152 mm) ± 1 in. (25 mm)
Operating Temperature	20° to 120°F (-7° to 49°C)
Storage Temperature	-20° to 150°F (-29° to 66°C)
Humidity	80% RH (noncondensing)
Water Resistance	Splash and water resistant, not waterproof