

### BL0873 OPTIMAX® High Solids

### Floor Care



#### Features

- 0% Free Styrene Acrylic Copolymer Finish & Sealer Combination
- 25% Solids
- UHS (1500+) Including Propane Effectiveness
- Spray Buffable or Restorable
- Covers Up to 3000 Sq. Ft. Per Gallon; Apply 2-4 Coats

#### Description

This product is a durable high solids coating, providing unsurpassed gloss with low maintenance requirements. This unique formula is designed for medium to heavy traffic areas with infrequent maintenance schedules to protect and improve the appearance of resilient, terrazzo and other flooring typically coated with conventional floor finish. Incorporates modern polymer technology to keep floors shining after heavy surface traffic abuse and is suitable for use with UHS electric, battery or propane high-speed buffing/burnishing programs.

TECHNICAL INFO:		
Physical Properties	Appearance	Milky
	Color	White
	Odor/Fragrance	Slightly Sweet
	pH	8.2 – 8.8
	Freeze/Thaw Stability	Good
Environmental Profile	Glycol Ether Content	Yes (E Series)
	Biodegradability	No
	Chlorinated Solvents	None
	Enviro Standard	N/A
	Recyclable Packaging	Yes
Regulatory Compliance	% VOC By Weight	<1%
	VOC Restricted Regions	None
	Food Processing Suitability	N/A
	EPA #	N/A
	Flammability per CPSC	N/A
	Flash Point	None to Boiling



Packages Available:



Label Datecode: 09/00