

PIG® HazMat Spill Kit in See-Thru Wall-Mount Chest

#KIT385 - Absorbs up to 21.25 gal. • No Wheels • Not UN Rated



Sturdy translucent container makes inventorying contents a breeze and ensures your kit is always ready to go.

- Transparent container lets you check supply levels at a glance
- PIG HazMat Socks stop spreading spills; PIG HazMat Pads and Pillows absorb; PIG Repair Putty plugs and patches cracks and leaks
- PIG HazMat Absorbents are specially treated for unsurpassed performance with concentrated corrosives, such as 98% sulfuric acid and 30% sodium hydroxide
- Prepacked container provides easy access to contents
- Large, color-coded label makes identification fast and accurate
- Temporary disposal bags help make cleanup easier
- Wall-mountable to save space and maximize visibility
- Only PIG Spill Kits feature PIG Absorbents proven for rapid response
- For information on custom spill kits, just call 1-800-HOT-HOGS (468-4647)

Always in stock. Ships within 24 hours.



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: KIT385 - Pg 1 of 2

KIT385 Specifications

Fluids Absorbed:	Acids, Bases & Unknowns
Absorbency:	Up to 21.25 gal.
Spill Volume:	20 - 29 gal.
Lift-out Basket:	No
Outdoor Storage:	No
UN Rated:	No
UV Resistant:	No
Wheels:	No
Sold as:	1 each
Weight:	47.62 lbs.
# per Pallet:	6
Composition:	Container/Mats/Socks/Pillows - Polypropylene Bracket - 11-Gauge Powder Coated Steel Putty - 15% Epoxy Resins 1.5% Catalyst 83.5% Non- Hazardous (Trade Secret) Ingredient
Includes:	50 - 15" W x 20" L PIG® HazMat Mat Pad (MAT301) 1 - ext. dia. 3" x 10' L PIG® HazMat Chemical Absorbent Sock (PIG301) 7 - ext. dia. 3" x 46" L PIG® HazMat Chemical Absorbent Sock (124CR) 2 - 17" W x 16" L x 2" H PIG® HazMat Chemical Absorbent Pillow (HR7015) 5 - 18" W x 30" H Polyethylene Disposal Bags (BAG201-S) 1 - Spill-Kit Station Sign (SGN566-130-ALM) 1 - 7" L PIG® Multi-Purpose Epoxy Putty (PTY201) 1 - 14"H x 5.63"D (2 parts) Wall-mount bracket 1 - Instructions
UNSPSC:	47131905

Technical Information

Warnings & Restrictions:

HAZ-MAT Notice

To ensure effectiveness and your safety, we recommend that you conduct compatibility and absorption testing of your chemicals with PIG® HAZ-MAT products prior to purchase. If you have any questions or need samples to test, please call Technical Services.

This product is subject to export restrictions and cannot be shipped to Canada or the European Union.

Technical Documents:

(Available at newpig.com)

Product Data Sheet (PDS)

Safety Data Sheet (SDS)

Chemical Compatibility (CCG)



KIT385 Metric Equivalent

Absorbency:	Up to 80.4 L
Weight:	21.6 kg



By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

New Pig

One Pork Avenue • Tipton PA 16684-0304
© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: KIT385 - Pg 2 of 2