

# PIG® Chat Mat® Gray Absorbent Roll

#MAT608 - Medium-weight • 24" x 75'



PIG Mat with a printed safety message. Keep floors dry while delivering a message that can't be ignored!

- Lasts 2X longer than ordinary mats for fewer change-outs, absorbs everything, works everywhere; that's why more plants worldwide use PIG Mat than any other brand
- Clearly visible messages are repeated down the length of the roll to help create a safer environment for workers
- Durable top layer prevents wear, even under heavy foot traffic
- Under the Chat Mat top layer is the proven eight-layer, 100% polypropylene construction of PIG Mat, the strongest mat on the market!
- Exclusive dimple pattern speeds wicking of liquid throughout mat for faster, easier cleanup
- Absorbs most common industrial liquids - oils, water, solvents, coolants and more
- Absorbed leaks and drips blend right in; dark gray color hides grime so mat stays on the job longer
- Flame-resistant material won't burn immediately like cellulose mats; melts when exposed to high heat while on the job
- Can be wrung out and incinerated after use to reduce waste or for fuels blending
- Easy-tear perforations let you take only what you need, so you use less mat and save money

Always in stock. Ships within 24 hours.



By Phone:  
**1-855-493-HOGS**

Online:  
**newpig.com**

Email:  
**hothogs@newpig.com**

**New Pig**

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.

PIG and the PIG logo are trademarks in the U.S. and other countries.

## MAT608 Specifications

|                          |                                  |
|--------------------------|----------------------------------|
| <b>Color:</b>            | Gray                             |
| <b>Mat Weight:</b>       | Medium-weight                    |
| <b>Fluids Absorbed:</b>  | Oils, Coolants, Solvents & Water |
| <b>Recycled Content:</b> | 40% Recycled Content             |
| <b>Absorbency:</b>       | Up to 13.5 gal. per bag          |
| <b>Absorbency per:</b>   | Up to 13.5 gal. per roll         |
| <b>Dispenser:</b>        | No                               |
| <b>Perforated:</b>       | Every 10" Lengthwise             |
| <b>Poly-Backing:</b>     | No                               |
| <b>UV Resistant:</b>     | No                               |
| <b>Sold as:</b>          | 1 roll per bag                   |
| <b># per Pallet:</b>     | 40                               |
| <b>Composition:</b>      | Polypropylene                    |
| <b>UNSPSC:</b>           | 47131901                         |

## Technical Information

### Warnings & Restrictions:

There are no known warnings and restrictions for this product.

### Regulations and Compliance:

29 CFR 1910.22(a)(2) - Floors in the workplace should be, "maintained in a clean and, so far as possible, a dry condition."

### Technical Documents:

(Available at [newpig.com](http://newpig.com))

Product Data Sheet (PDS)

Safety Data Sheet (SDS)

Chemical Compatibility (CCG)



## MAT608 Metric Equivalent

|                        |                       |
|------------------------|-----------------------|
| <b>Absorbency:</b>     | Up to 51.1 L per bag  |
| <b>Absorbency per:</b> | Up to 51.1 L per roll |



**New Pig**

By Phone:  
**1-855-493-HOGS**

Online:  
**newpig.com**

Email:  
**hothogs@newpig.com**

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.

PIG and the PIG logo are trademarks in the U.S. and other countries.