

PIG® Low-Profile Pipe Leak Diverter with Flaps

#TLS191 - 11.5" x 9"



Leaky pipe in a tight spot? Low-profile design is great for capturing leaks where full-size designs can't fit.

- Low-profile design and compact size let you target a specific leak in tight spaces
- Flaps wrap around pipes and valves to capture drips and accumulated condensation as well as to contain spray from pressurized lines
- Nonpermeable material is vinyl-coated for strength and durability; resists punctures and mildew for long life
- UV resistant up to 12 months for long-term outdoor use without degradation
- Built-in grommets and rubber straps (sold separately) make it easy to hang from an overhead pipe
- Accepts a standard 3/4" hose connection to safely channel liquid to floor drain or collection container (hose sold separately)
- Flow rate of 3.33 gallons per minute when used with a 1/2" ID hose
- Need a custom size or solution? Just call 1-800-HOT-HOGS (468-4647)



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: TLS191 - Pg 1 of 3

TLS191 Specifications

Use With:	Pipes
Drainage Hose Included:	No
Flow Rate:	3.33 gal. per Minute
Grommets/D-Rings:	14 Grommets
Hanging Straps Included:	No
Hose Connector:	.75"
Installation Method:	Hanging Straps
Thickness:	16 mil
Sold as:	1 each
Composition:	67% PVC, 33% Polyester
UNSPSC:	24141506

Technical Information

Warnings & Restrictions:
Chemical Resistance
Limited chemical-resistance; not suitable for temperatures over 190° F/88° C.

Technical Documents:
(Available at newpig.com)
Product Data Sheet (PDS)



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304
© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: TLS191 - Pg 3 of 3