

GOOD

## Economy Bun Pan Rack

Model No.	Size W-H-L	Pan Cap.	Runner Spacing	Ship Wt.
<b>KNOCKED-DOWN UNITS - 5" stem type casters (#C480).</b>				
6300.....	20-3/8" x 69" x 26".....	30.....	2".....	49#
6301.....	20-3/8" x 69" x 26".....	20.....	3".....	39#
6303.....	20-3/8" x 69" x 26".....	12.....	5".....	32#
<b>ALL WELDED UNITS - 5" stem type casters (#C480).</b>				
6330.....	20-3/8" x 69" x 26".....	30.....	2".....	50#
6331.....	20-3/8" x 69" x 26".....	20.....	3".....	40#
6333.....	20-3/8" x 69" x 26".....	12.....	5".....	33#

**OPTIONS:**

"CL(A)", "PS", "VB" - see page 69 for details  
 \*\* PS option available for all welded units only\*\*

**ALL WELDED UNITS - 5" platform type casters (#C453).**

7331.....	20-3/8" x 69-3/4" x 26".....	20.....	3".....	45#
-----------	------------------------------	---------	---------	-----

**OPTIONS:**

"B", "CL(B)", "PB", "PS", "VB" - see page 59 for details.



#7331 • #6331 • #6301

- Accommodates 13" x 18", 14" x 18", and 18" x 26" sheet pans.



## Folding Bun Pan Rack

GOOD



#98678

Note: For heavy duty transport racks, see our 1300 Series Racks on page 1 or our Lifetime Series Racks on pages 10-12.

Model No.	Size W-H-D	Pan Cap.	Runner Spacing	Ship Wt.
98678.....	21" x 72" x 26".....	18.....	3".....	75#

Four 5" platform type casters - 2 swivel (#C483), 2 swivel w/ brake (#C482).

- Ideal for set-up and preparation for offsite and non-traditional locations.
- Units will hold 13" x 18", 14" x 18", and 18" x 26" pans.
- Four, one inch welds per aguide.
- Lifetime warranty against rust and corrosion, superior strength and durability guaranteed.



Model No.	Size W-H-D	Runner Spacing	Pan Capacity	Ship Wt.
98000...	23-1/4" x 31-1/4" x 26".....	1-1/2".....	12.....	50#
98001.....	23-1/4" x 37" x 26".....	1-1/2".....	16.....	52#
98179.....	23-1/4" x 37" x 26".....	3".....	8.....	50#

Equipped with four 5" platform type swivel casters (#C450), two with brake (#C455).

Vertical Corner Bumpers (4) are standard.

Note: Models #98000 & #98001 hold pans by the lip.

**Options:**

"B", "E", "MD", "PB", "PS" — See page 59 for details.



## Slicer/Mixer Stand



Outrigger Channels

#98000