

Flat Dollies



- One piece aluminum sheet design.
- Two inch sides with open corners for easy cleaning.
- Lifetime warranty against rust and corrosion.



Model No.	Size W-H-D	With Handle	Ship Wt.
-----------	------------	-------------	----------

CHILLTRAY DOLLY

99260.....	19" x 6" x 23-1/2"	No.....	13#
99260H.....	19" x 32-1/2" x 25-1/4"	Yes.....	17#

GLASS RACK DOLLY

99261.....	21" x 6" x 21"	No.....	15#
99261H.....	21" x 32-1/2" x 22-3/4"	Yes.....	20#

BUN/DOUGH DOLLY

99262.....	18-3/8" x 6" x 26-1/2"	No.....	15#
99262H.....	18-3/8" x 32-1/2" x 28-1/4"	Yes.....	18#

EMPTY LUG DOLLY

99251.....	17" x 6" x 26"	No.....	13#
99251H.....	17" x 32-1/2" x 27-3/4"	Yes.....	17#

CHICKEN CASE DOLLY

99263.....	15-1/4" x 6" x 23"	No.....	15#
------------	--------------------	---------	-----

Four 3" x 1-3/8" platform type swivel casters (#C410).

Pan Dollies



#1193 • #1194 • #1192

- Transport and store 13" x 18 and 18" x 26" pans.

Model No.	Size W-H-D	Wt. Cap.	Ship Wt.
-----------	------------	----------	----------

ANGLE DOLLY WITHOUT SIDES OR HANDLE

1192.....	18-7/8" x 7" x 27"	800#	20#
-----------	--------------------	------	-----

ANGLE DOLLY WITH SIDES & HANDLE

1193.....	21" x 33-1/2" x 27"	1000#	22#
-----------	---------------------	-------	-----

TWO TIER ANGLE DOLLY WITH SIDES & HANDLE

1194.....	21" x 44-1/2" x 30"	1200#	29#
-----------	---------------------	-------	-----

ALUMINUM DRAG HOOK

1199.....	37-1/2" Long		1#
-----------	--------------	--	----

Four 5" platform type swivel casters (#C453).

Options:

"CL(B)", "MD", "PP(A)" — see page 63 for details.



Super Dolly



#1182



#1199

Model No.	Size W-H-D	Wheel Size	Wt. Cap.	Ship Wt.
-----------	------------	------------	----------	----------

1181.....	24" x 10" x 29-1/2"	6"	2800#	30#
1182.....	24" x 8" x 29-1/2"	5"	1100#	18#

ALUMINUM DRAG HOOK

1199.....	37-1/2" Long			1#
-----------	--------------	--	--	----

Four platform type casters - two swivel, two rigid.

#1181= 2 swivel (#C490) 2 rigid (#C500)

#1182 = 2 swivel (#C450) 2 rigid (#C460)

Options:

"B", "CL(C)" (Model #1181), "CL(B)" (Model #1182) - see page 63.

