

Heavy Duty Lug Carts

Model No.	Size W-H-D	Lug Cap.	Ship Wt.
HEAVY DUTY - Accepts 16" x 8-1/2" x 25" Lug (Not Included)			
1261.....	18-3/4" x 27-1/2" x 21"	2	23#
1262.....	18-3/4" x 52" x 26-1/2"	4	33#
1263.....	18-3/4" x 72" x 26-1/2"	6	41#
93136*.....	29-1/2" x 38" x 32-1/2"	6	28#
1264.....	29-1/2" x 62" x 33"	10	48#

MODEL #1261 REQUIRES STACKING LUGS

#1261, #1262, & #1263 has four 5" plate type swivel casters (#C450). #1264 has four 5" platform type casters; two swivel with brake (#C465), two rigid (#C475).

OPTIONS:

"CL(B)" (#1261, #1262 & #1263 only) — See page 63 for details.

STANDARD - Accepts 16" x 8-1/2" x 25" Lug (Not Included)

1265.....	15-3/4" x 19" x 26"	1	11#
1266.....	15-3/4" x 33" x 28-1/4"	2	14#
1267.....	Handle for #1265 & #1266 (bolted on)		

STANDARD - With Welded Handle

1265H.....	15-3/4" x 36-1/2" x 28 3/8"	1	14#
1266H.....	15-3/4" x 36-1/2" x 30-1/2"	2	18#

Four 5" stem type casters (#C480).

* Not NSF Approved

OPTIONS:

"CL(A)", "MD" — See page 63 for details.



E-Z Load Lug/Pick Cart

Model No.	Size W-H-D	Wt. Cap.	Ship Wt.
99304.....	15-3/4" x 41-1/2" x 28"	500#	20#

Four 5" stem type casters (#C480).

- Designed for easy loading and unloading.
- Top frame holds standard lug tube on cross supports.
- All welded aluminum construction.



#99304

