

# Mobile Dunnage Rack

BETTER



Mobile Dunnage Rack



Model No.	Size D-H-L	Wt. Cap.	Ship Wt.
1201.....	20" x 8-1/4" x 25-3/4"	1200#	17#
1211.....	20" x 8-1/4" x 31-3/4"	1200#	19#
1202.....	20" x 8-1/4" x 37-3/4"	1200#	19#
1200.....	20" x 8-1/4" x 43-3/4"	1200#	21#
1203.....	20" x 8-1/4" x 49-3/4"	1200#	22#
1212.....	20" x 8-1/4" x 61-3/4"	1200#	24#
1208.....	Handle for 20" W Units Above		4#
1213.....	24" x 8-1/4" x 25-3/4"	1200#	20#
1214.....	24" x 8-1/4" x 31-3/4"	1200#	19#
1204.....	24" x 8-1/4" x 37-3/4"	1200#	20#
1205.....	24" x 8-1/4" x 43-3/4"	1200#	21#
1206.....	24" x 8-1/4" x 49-3/4"	1200#	22#
1207.....	24" x 8-1/4" x 61-3/4"	1200#	25#
1174.....	Handle for 24" W Units Above		4#

Four 5" plate type casters: (2)swivel w/ brake (#C455), (2)rigid (#C460)

**OPTIONS:**

**Heavy Duty Casters** -Add "HD6" suffix to model #.

Four 6" plate type casters:(2) swivel w/ brake (#C495), (2) rigid (#C500).

**All Swivel Casters** -Add "SW" suffix to model #.

BETTER

# Stacking Dunnage Rack



Model No.	Size D-H-L	Wt. Cap.	# of Lat.	Ship. Wt.
97168.....	18" x 12" x 24"	3200#	4	8#
97169.....	18" x 12" x 36"	3200#	4	10#
97170.....	18" x 12" x 48"	2700#	4	12#
97171.....	20" x 12" x 24"	3200#	4	9#
97172.....	20" x 12" x 36"	3200#	4	10#
97173.....	20" x 12" x 48"	2700#	4	12#
97174.....	24" x 12" x 24"	3200#	5	10#
97175.....	24" x 12" x 36"	3200#	5	12#
97176.....	24" x 12" x 48"	2700#	5	14#

Note: The Width & Depth Listed Above Are The "Footprint" Dimensions.

# Dunnage Rack

GOOD



Model No.	# of Lat.	Wt. Cap.	Size D-H-L	Ship Wt.
6017.....	4	2000#	20" x 8" x 36"	8#
6018.....	4	2000#	20" x 8" x 48"	10#
6019.....	4	1500#	20" x 8" x 60"	12#
6004.....	4	2000#	20" x 12" x 36"	8#
6005.....	4	2000#	20" x 12" x 48"	10#
6006.....	4	1500#	20" x 12" x 60"	12#
6014.....	5	2000#	24" x 8" x 36"	9#
6015.....	5	2000#	24" x 8" x 48"	12#
6016.....	5	1500#	24" x 8" x 60"	14#
6008.....	5	2000#	24" x 12" x 36"	10#
6009.....	5	2000#	24" x 12" x 48"	12#
6010.....	5	1500#	24" x 12" x 60"	15#