

Produce/Stocking Cart



#1415



#1420



#1490



Model No	Size W-H-L	Wt. Cap.	No. Casters	Top Shelf Height	Ship Wt.
SOLID TOP SHELF • T-BAR BOTTOM SHELF					
1415.....	19" x 30" x 41"	800#	4	30"	43#
SOLID TOP SHELF • T-BAR BOTTOM SHELF W/ HANDLE					
1416.....	19" x 39" x 48"	800#	4	30"	52#
T-BAR TOP & BOTTOM SHELF W/ HANDLE					
1420.....	19" x 39" x 48"	1200#	4	30"	52#
SOLID TOP & BOTTOM SHELF W/ HANDLE					
1490.....	19" x 39" x 48"	800#	6	30"	55#

Model #1415, #1416 & #1420: Four 5" platform type casters; two swivel (#C450) two rigid (#C460).
Model #1490: Six 5" platform type casters - four swivel (#C450) two rigid (#C460).

OPTIONS: *** FACTORY INSTALLED ONLY***

"CL(B)", "PB" — See page 59 for details.

- These all welded units provide maximum strength and durability.
- Raised marine edge on solid shelves contain spills.
- T-Bar type shelves provide air circulation.
- Lifetime warranty against rust and corrosion.
- NSF Certified.

Model No	Size W-H-L	Wt. Cap.	Top Shelf Type	Top Shelf Height	Ship Wt.
NS557	21" x 44" x 59-1/2"	3000#	Bar	30"	63#

Unit With Solid Aluminum Top

NS557A ..	21" x 44" x 59-1/2"	3000#	Solid	30"	65#
-----------	---------------------	-------	-------	-----	-----

Two tier unit with handle.

Four 6" x 2" platform type casters: two swivel w/ brake (#C495), two rigid (#C500).

OPTIONS:

"B", "PB", "VB" -- See page 59 for details.

- For use in any application that requires maximum strength and durability.
- All welded aluminum construction with four, 6" x 2" platform type casters.
- 3000# Weight capacity
- Lifetime warranty against rust and corrosion.
- NSF Certified.

Heavy Duty Stock Truck



#NS557

