

U-Shaped Platform Truck



#99321

Model No.	Size W-H-L	Deck Size	Wt. Cap.	Ship Wt.
99320.....	20" x 44-1/2" x 36-1/2"	20" x 36"	2000#	47#
99321.....	20" x 44-1/2" x 48-1/2"	20" x 48"	2000#	50#
99322.....	20" x 44-1/2" x 60-1/2"	20" x 60"	2000#	53#
99323.....	30" x 44-1/2" x 48-1/2"	30" x 48"	2000#	57#
99324.....	30" x 44-1/2" x 60-1/2"	30" x 60"	2000#	61#

Four 8"x2" platform type casters - 2 swivel (#C526), 2 rigid (#C527).

Options:

"CL(C)", "PB", "PP(C)"— see page 63 for details.

- Channel deck for heavy duty loads and easy cleaning.
- Deck Height = 11-1/4"
- Rounded nose decreases damaged walls and doors.
- Removable tube handle.
- Lifetime warranty against rust and corrosion.



Folding Platform Truck



#98667

Model No.	Size W-H-D	Position	Wt. Cap.	Ship Wt.
98667.....	26-1/4" x 51-9/16" x 48"	Unfolded	800#	68#
	26-1/4" x 12" x 48"	Folded		

Four 6" heavy duty plate casters - 2 swivel (#C530), 2 rigid (#C531).

- Handle folds up for easy storage.
- Has 8-3/4 square feet of deck space... Takes up less than 3 square feet of storage space.
- For transporting heavy loads from the back room to the floor.
- Lifetime warranty against rust and corrosion.



"Don't Compromise....Customize."



#99733



#99631



#99361

