

# OLW™

## OUTDOOR LED WALL PACK

*Delivering the promise of LEDs with two high-output additions to the OLW family of wall packs.*



**OLW 23 / OLW 31**



The sleek, contemporary design of the OLW 23 and OLW 31 is offered in two new lumen packages to meet a wide variety of your lighting needs.

*The OLW 23 / OLW 31 LED wall pack at a glance:*

- High-performance LED technology deliver 2,252 or 3,073 lumens.
- Precision engineered optical lens are more efficient than competitors' reflector-style wall packs.
- Wide, Type III, light distribution uniformly illuminates walkways, commercial driveways and more.
- Adjustable MVOLT photocell, standard.
- Nighttime Friendly™ full cutoff above 90° angle, standard.
- 6kV surge protection, standard
- Junction box for surface- or recess-mounting options

[www.lithonia.com/OLW](http://www.lithonia.com/OLW)

**Related LED products:**



OFLR Security Floodlights



OLAW LED Area/Wall Light



OLW14 LED Wall Pack

**Value and versatility** *defined*








# OLW™

## OUTDOOR LED WALL PACK

DESIGNLIGHTS  
CONSORTIUM

### OLW Family REFERENCE CHART

			
<b>Model No.</b>	OLW14	OLW 23	OLW 31
<b>Replaces</b>	50W Metal Halide	100W Metal Halide	250W Metal Halide
<b>Input Watts</b>	26	35	48
<b>Delivered Lumens</b>	1436	2252	3073
<b>Lumens per watt</b>	54	64	64
<b>CRI</b>	77	69	69
<b>Light Color (CCT)</b>	5700K	5000K	5000K
<b>Nighttime Friendly™</b>	with optional shield	Standard	Standard
<b>No. of LED's</b>	8	10	14
<b>Voltage</b>	120V-277V	120V-277V	120V-277V
<b>Photocell</b>	Standard	Standard	Standard
<b>Surge Suppression</b>	6000 Volts	6000 Volts	6000 Volts
<b>Warranty</b>	5 years	5 years	5 years
<b>Weight</b>	3.4 lbs	7.3 lbs	7.3 lbs
<b>Mounting</b>	Surface or recessed mount	Surface, recessed or arm mount	Surface, recessed or arm mount
<b>Light Distribution</b>	Type I	Type III	Type III

#### ORDERING INFORMATION

For shortest lead times, configure products using **bolded options**.

**Example: OLW 23**

OLW	23			
Series	Lumens / Color Temperature	Voltage	Features	Finish
<b>OLW</b> LED Wall Light	<b>23</b> 2300 delivered lumens / 5152K <b>31</b> 3100 delivered lumens / 5223K	<b>(blank)</b> MVOLT (120V-277V)	<b>(blank)</b> Photocell included	<b>(blank)</b> DDB Dark Bronze

Accessories: Order as separate catalog number.

OMA M6 14" Aluminum Mounting Arm

