

OTTO
Expect Excellence.

HURRICANE II HEADSET

Recommended for public safety markets, manufacturing, airline industries and all users in high noise environments.



The **Hurricane II headset** is designed to provide the performance of a heavy duty headset in a high noise environment without all of the weight and bulk. The dual ear loops ship standard with NoisEzSM Ear Tips with an NRR rating of 29dB, delivering advanced protection against dangerous decibel levels. The user can easily convert the headset for use in a low noise environment by simply switching out the ear tips. The close fitting headset can be worn comfortably under a helmet or cap.

Mechanical Specifications:

- Cable pull from T module, axial: 30 lbs
- Cable pull from headset, axial: 20 lbs
- Wire pull from receiver, axial: 20 lbs
- Receiver wire pull from headset, axial: 20 lbs
- Flex at connector: 25,000 cycles
- Cable flex at T module: 6,000 cycles
- Cable flex at headset: 15,000 cycles
- Cable flex at receiver: 5,000 cycles
- Wireform flex (tip to tip): 25,000 cycles
- 24 month manufacturer's warranty

Electrical Specifications:

- Microphone sensitivity at 94dB SPL: -44 typical

Environmental Specifications:

- Operating temperature: -20° C to +60° C
- Storage temperature: -40° C to +80° C

Grainger Item #6XTR7/ Mfr. Model #V4-HN2MG5
Grainger Item #6XTU2/ Mfr. Model #V4-HN2MM5
Grainger Item #6XUC6/ Mfr. Model #V4-HN2CM1
Grainger Item #6XTW0/Mfr. Model #V4-HN2MF3B
Grainger Item #6XTV1/ Mfr. Model #V4-HN2MJ5
Grainger Item #6XTW4/Mfr. Model #V4-HN2MA5
Grainger Item #6XTL3/ Mfr. Model #V4-HN2KA5
Grainger Item #6XTP3/ Mfr. Model #V4-HN2KB1
Grainger Item #6XTZ5/ Mfr. Model #V4-HN2VJ5
Grainger Item #6XTR2/ Mfr. Model #V4-HN2ME5
Grainger Item #6XTY6/ Mfr. Model #V4-HN2VD5
Grainger Item #6XUD8/ Mfr. Model #V4-HN2EJ1
Grainger Item #6XUA6/ Mfr. Model #V4-HN2CS3B

For more information contact your Grainger Representative or visit Grainger.com[®]

AVAILABLE THROUGH

GRAINGER[®]

FOR THE ONES WHO GET IT DONE