



**FA/GZL SERIES
GAS CONVECTION OVENS
REPLACEMENT PARTS LIST**

EFFECTIVE APRIL 19, 2012

Superseding All Previous Parts Lists.

The Company reserves the right to make substitution in the event that items specified are not available.

ERRORS: Descriptive and/or typographic errors are subject to correction.

BLODGETT OVEN COMPANY

44 Lakeside Avenue, Burlington, Vermont 05401 USA Telephone: (802) 658-6600 Fax: (802) 860-3732
www.blodgett.com

P/N 52922

IMPORTANT: When ordering parts, please provide the model, gas type and serial number of the oven. The identification plate is located on the left side of the combustion compartment and, also, above the control panel under the ledge.

☑ ASAP Distributor Required Stocking Parts
 ◆ Doors Are Not Returnable
 * Item Is Too Large For UPS

ELECTRICAL COMPONENTS

Ref. No.	Part No.	Description
	5147	Timer, 60 Minute Mechanical w/Knob
	16498	Knob Only, 60 Minute Mechanical Timer (After 5/83)
	10465	Knob Only, 60 Minute Mechanical Timer (Before 5/83)
	11304	Dial Only, 60 Minute Mechanical Timer
	15956	Timer, 60 Minute Electrical
	16686	Knob, 60 Minute Electrical Timer
	16948	Timer, 60 Minute for Buzzer
	16030	Knob Only, 60 Minute for Buzzer
	11427	Timer, 6 Hour for Buzzer w/Knob
	20349	Electric Buzzer Only, 115V
	20350	Electric Buzzer, 208-240V
	4342	Interior Lamp
	4922	Lamp Socket
	4908	Indicating Lamp 1 3/8" x 7/8" (Before 12/68)
	6504	Indicating Lamp 1 3/8" x 1/2" (for 208V Ovens)
	15549	Indicating Lamp (115V)
	11200	Terminal Block
	11261	Transformer Hi-Volt 408V to 120V
	35918	Microswitch, Door Replaces 19978
	6195	Bracket, Mounting for Microswitch
	5091	Cord Set
	6496	Switch, SPST, Rocker, Blue, 115V (Blower)
	4907	Switch, SPST, Toggle, White 115V (Blower & Lights)
	6497	Switch, SPST, Rocker, White 115V (Lights)
	6498	Switch, SPDT, Rocker, Red 115V (Cool Down)
	6500	Switch, DPST, Rocker, Blue 208V, for 3PH (Blower)
	9979	Switch, DPST, Toggle Replacement, White 208V for 3PH (Blower & Lights)
	6501	Switch, DPST, Rocker, White 208V for 3PH (Lights)
	6502	Switch, DPDT, Rocker, Red 208V for 3PH (Cool Down)
	7149	Switch, 3PST, Rocker, Black 208V for 3PH, 1SP (Blower)
	6499	Switch, SPDT, Rocker, Black 115V, 1PH, 2SP (Blower)
	6503	Switch, DPDT, Rocker, Black 208V, 1PH, 2SP (Blower)
	7636	Switch, 3PDT, Rocker, Black, 115V, 3PH, 2SP (Blower)
	32232	Motor, 115/230V, 1SP, 1/3HP, 1PH
	32244	Motor, 230V, 2SP, 1/3HP, 1PH
	32268	Motor, 208-230/460V, 1 SP, 1/3HP, 3PH,
	32334	Motor, 460V, 2SP, 1/3HP, 3PH

ELECTRICAL COMPONENTS - cont'd

Ref. No.	Part No.	Description
	32256	Motor, 115V, 1PH, 2SP 1/3HP
	91105	Motor Conversion Kit, 3PH to 1PH, 2SP
	NOTE:	Use this kit for units with 2SP, 3PH feature
	5001	Blower Wheel, 10" Diameter

BURNER & PIPING ASSEMBLY

Ref. No.	Part No.	Description
	8324	Steel Tube Burners (Set of 2) FA
	8325	Steel Tube Burners (Set of 2) GZL
	16361	Air Shutter Only
	3001	Locknut Only (for Air Shutter)
	8726	Manifold
	8717	Orifice, Set of 2 (Specify Model & Gas Type)
	4872	Manifold Plug 1/8"
	251	Manifold Coupling
	10252	Union, Ell 1/2"
	1949	Nipple, 1/2" x Close
	5115	Ell 1/8 to 3/16 Flared Tubing
	11528	Thermostat & Nipple, FDO w/Knob (150-500°)
	10564	Dial/Knob for FDO Thermostat
	7854	Gas Valve w/Handle & Screws
	7855	Handle Only for Gas Valve
	11334	Pilot Burner For FMEA (Nat)
	11335	Pilot Burner For FMEA (LP)
	5386	.018 Pilot Orifice-FM (Nat)
	5387	.010 Pilot Orifice-FM (LP)
	8922	Tubing for Pilot Burner
	5118	Gas Pressure Regulator (Nat)
	11504	Gas Pressure Regulator (LP)
	31258	Pressure Switch (LP)
	2646	Nut, Flared Tubing 3/16"
	8733	Deflector Assy, w/Burner Divider FA
	18875	Deflector Assy, "Dog Legs" (Set of 4)
	8734	Deflector Assy, w/Burner Divider GZL
	11237	Burner Divider Only, FA
	11254	Burner Divider Only, GZL
	9166	Combustion Compartment Shield
	20107	Conversion Kit, LP to Nat, FA
	20108	Conversion Kit, Nat to LP, FA

ELECTRIC IGNITION

Ref. No.	Part No.	Description
	17952	Electric Ignitor
	20287	Solenoid Valve
	11513	Electric Thermostat (500° F)
	16393	Dial Knob for Thermostat
	21436	Base & Bracket for TDR
	16372	Fuse, 5 AMP

COOK & HOLD CONTROLS

Ref. No.	Part No.	Description
	16392	Knob for Hold Thermostat (120-200)
	15365	Electric Hold Thermostat (120 - 200 F)
	91182	Contact, 35 AMP
	10465	Knob, Timer-Pointer
	20287	Solenoid Valve
	11513	Electric Cook Thermostat (500 F)
	16393	Knob for Cook Thermostat
	11281	Dial Timer 12 Hour Cook & Hold
	15363	Hold Indicator Light (High Volt)

BAKING COMPARTMENT COMPONENTS

Ref. No.	Part No.	Description
	8727	Compartment Liner Bottom FA-100 Porcelain
	8730	Compartment Liner Bottom GZL, S/S
	8724	Rack Supports FA-100 (Set of 2)
	8636	Rack Supports GZL-10 (Set of 2)
	4701	Racks (Each) 20 7/8" x 28 1/4" FA
	6330	Racks (Each) 27 7/8" x 28 1/4" GZL
	8648	Screws for Baffle (Set of 4)
	8646	Support Brackets, Baffle (Set of 4)
	20642	Light Guard, Baffle
☑	5001	Blower Wheel, 10" Diameter
	10062	Motor Mount & Panel Assy.
	8725	Thermostat Bulb Clip

DOOR COMPONENTS

Ref. No.	Part No.	Description
	912	Brass Bushings (Welded)
	8583	Door Catch (Striker Plate w/Screws)
	8584	Door Catch (Ball Plunger w/Nut)
	5742	Spanner Key for Ball Plunger Latch
	4887	Chain & Turnbuckles
	9978	Sprocket Assy.
	11698	Cam Assy., Door Switch
	11867	Glass Assy. w/Supports 20 1/2" x 14 1/4" (Replaces 8812 Window, 22 3/8" x 16")
	20641	Window Support Brackets
	10233	Handle, 21" (Before 12/81)
	11080	Hinge Pins w/ Bolts (Set of 4)
	8846	Hinge Pin Bolts (Each)
	11172	Lower Hinge Pin w/Bolts (Square)
	11173	Upper Hinge Pin w/Bolts (Round)
	90010	Perimeter Gaskets, S/S
	10471	Center Door Gasket, Metal (Set of 2)
	11695	Washers (Set of 12)
	35918	Microswitch, Door Replaces 19978
	6195	Bracket, Mounting for Microswitch

FOR OVENS MANUFACTURED BEFORE 6/76 W/OLD STYLE DOORS

9037	Window, 17 1/8" x 10 3/16"
9038	Handle, 20"
8608	Hinge Pins w/ Screws
11320	Upper Hinge Pin w/Screws (Round)
11321	Lower Hinge Pins w/Screws (Round)
4155	Screw for Upper Hinge Pin (Allen Head) Each
4832	Screw for Lower Hinge Pin (Allen Head) Each
7801	Center Door Gasket

NOTE: S/S Perimeter Gaskets Replace both fiberglass and silicone gaskets fitted to earlier ovens. Units manufactured before 3/67 require Perimeter Gasket w/ Side Trim, Part Number 11541.

EXTERIOR COMPONENTS

<u>Ref. No.</u>	<u>Part No.</u>	<u>Description</u>
	8709	Draft Hood & Adapter, Direct Vent FA-100 (6" Diameter)
	7840	Draft Diverter, Canopy Vent, FA-100/GZL-10 S/S
	20447	Draft Diverter, Canopy Vent, FA-102/GZL-20, S/S
	20443	Flue Box (Sgl Stack)
	17943	Flue Connector (4 Pces.) FA-102/GZL-20 (Dbl Stack)
	23190	Crown Assy., FA
	8600	Legs, 6", S/S (Set of 4)
	8598	Legs, 25", S/S (Set of 4)
NOTE: Legs are sold only as Sets of 4		
	7847	Leg Bolts (Set of 8)
	92000	Leg Studs (Set of 4)
	9012	Handle, Burner Door
	8716	Control Compartment Cover
	6486	Open Stand w/Feet, S/S FA
	11416	Open Stand w/Casters, S/S FA
	5779	Caster Kit w/Plate, Set of 4 (Dbl)
	16002	Casters, Set of 4 (Sgl)
	11255	BLODGETT Nameplate
	20326	Lighting Instruction Plate

ROLL-IN UNITS & PARTS

(FA USES S9; GZL USES L9)

<u>Ref. No.</u>	<u>Part No.</u>	<u>Description</u>
	8355	Docking Pins, Transport Cart (Set of 2)
	8356	Casters, 5" for Transport Cart (Set of 4)
	9052	Handle, Transport Cart (Single Unit)
	8359	Catch Mechanism, Transport Cart
	8357	Locking Bar, Transport Cart
	8358	Tracks & Shelf Assy., Transport Cart
	9015	Handle, Double Transport Cart
	7931	Vertical Posts, Each
	7689	Transport Cart, CTRG
	8626	Transport Cart, CTRG-2
	7365	Roll-In Basket Dolly, DBRI-L
	7969	Roll-In Basket Dolly, DBRI-S
	11206	Roll-In Pan Rack, RPR-L9 w/5 Racks
	11207	Roll-In Pan Rack, RPR-S9 w/5 Racks
	7590	Racks for Pan Rack, L9
	8677	Racks for Pan Rack, S9