



CorePro LED Lamps

10.5A19/COREPRO/3000 6/1

Philips CorePro LED Lamps provide an energy efficient lighting solution

Product data

• General Characteristics

Cap-Base	E26
Bulb	A60 [A 60mm]
Rated Avg. Life (Hours)	15000 hr
Nominal Lifetime hours	15000 hr

• Light Technical Characteristics

Color Code	WW
Color Designation	White
Correlated Color Temperature	3000 K
Approximate Lumens	800 Lm
CRI	80
Luminous Efficacy Lamp	76.19 Lm/W
Color Temp. (Kelvin)	3000 K [CCT 3000K]
Rated Luminous Flux	800 Lm
LLMF - end nominal lifetime	70 %
Colour consistency	6 steps

• Electrical Characteristics

Wattage	10.5 W
Wattage Technical	10.5 W
Voltage	120 V
Line Frequency	50-60 Hz
Power Factor	0.7 -
Lamp Current mA	103 mA
Dimmable	No
Wattage Equivalent	60 W

Rated Wattage	10.5 W
Starting Time	0.5 s
Suitable for accent lighting	No

• Temperature Characteristics

• Environmental characteristics

Energy Efficiency Label (EEL)	A
-------------------------------	---

• Measuring Conditions

Switching cycle	50000X
-----------------	--------

• Product Dimensions

Overall Length C	99.3 mm
Diameter D	59.3 mm

• Product Data

Product number	430512
Full product name	10.5A19/COREPRO/3000 6/1
Short product name	10.5A19/COREPRO/3000 6/1
Pieces per Sku	1
eop_pck_cfg	6
Skus/Case	6
Bar code on pack	46677430511
Bar code on case	50046677430516
Logistics code(s)	929000220404
eop_net_weight_pp	0.074 kg



PHILIPS

Warnings and Safety

- Suitable for use in damp locations.
- Not for use in totally enclosed luminaires.
- Before replacing, turn off power and let lamp cool to avoid electrical shock or burn.



© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, April 10
data subject to change