



**MODEL FC1500HBP2**  
**1.5 HP SINGLE-STAGE COMPRESSOR**  
**DIRECT DRIVE**

**Only  
 20" Tall  
 &  
 37 lbs!**



**ROLAIR STANDARD FEATURES**

- PUMP:** ROLAIR Quality, Single Stage, Ball Bearings, Cast-Iron Cylinder, Stainless-Steel Reed Valves and Splash Lubrication Ensure Longer Life.
- MOTOR:** 1.5 HP, 3400 RPM, Low-Amp Draw, Overload Protection with Manual Reset, 115 Volt, 60 Hz, Heavy-Duty/Industrial-Grade with Ball Bearings for Greater Durability.

**SPECIFICATIONS**

MODEL	MOTOR HP	# OF CYLS	CU. FT. DISPLACED	CU. FT. DELIVERED	TANK CAP.	DIMENSIONS (L X W X H)	APPROX. SHIPPING
FC1500HBP2	1.5	1	7.8	4.0	1.5	13 X 12 X 20	39

**STANDARD EQUIPMENT**

- Start/Stop Pressure Switch with On/Off Lever
- Air Line Regulator and Pressure Gauge
- Compact/Lightweight Tank Design
- Tank Pressure Gauge
- Safety-Relief Valve
- Replaceable Filter Cartridge
- Initial 6 oz. Oil Fill Included
- 13.5 Amp Motor



606 South Lake Street > P.O. Box 346 > Hustisford, WI 53034-0346 > **920.349.3281** > fax 920.349.3691 > [www.rolair.com](http://www.rolair.com)



**Only  
39 lbs!**



### ROLAIR STANDARD FEATURES

- PUMP:** ROLAIR Quality, Single Stage, Ball Bearings, Cast-Iron Cylinder, Stainless-Steel Reed Valves and Splash Lubrication Ensure Longer Life.
- MOTOR:** 1.5 HP, 3400 RPM, Low-Amp Draw, Overload Protection with Manual Reset, 115 Volt, 60 Hz, Heavy-Duty/Industrial-Grade with Ball Bearings for Greater Durability.

### SPECIFICATIONS

MODEL	MOTOR HP	# OF CYLS.	CU. FT. DISPLACED	CU. FT. DELIVERED @ 90 PSI	TANK CAP. (GAL.)	DIMENSIONS (L X W X H) (INCHES)	APPROX. SHIPPING WT. (LB.)
FC1500HS3	1.5	1	7.8	4.0	2.5	20 X 9 X 18	43

### STANDARD EQUIPMENT

- Start/Stop Pressure Switch with On/Off Lever
- Air Line Regulator and Pressure Gauge
- Compact/Lightweight Tank Design
- Tank Pressure Gauge
- Safety-Relief Valve
- Replaceable Filter Cartridge
- Initial 6 oz. Oil Fill Included
- 13.5 Amp Motor