

2-DRAWER LEGAL VERTICAL FIRE FILE - 31" DEEP

2G3100P/2G3100B/2G3100L

Schwab reference #: 2CFD-5000

P - Putty B - Black L - Light Gray



PROTECTION FEATURES:

- UL Classified Fire Endurance (1 hour at 1700° F)
 - Protects documents, records and valuables against catastrophic loss
- UL Classified Explosion Hazard Resistance
 - Design integrity protects contents against explosions in case of sudden exposure to intense heat

SECURITY FEATURES:

- Plunger key lock secures all drawers
- Drawer-specific "lock/unlock" provision
 - Provides additional security by isolating access to specific drawers

INTERIOR FEATURES:

- Lined interior conceals cabinet insulation and protects contents from unwanted dust
- Rugged suspension system design
 - Ensures smooth and easy drawer movement – even when fully loaded
- Drawer layout flexibility accommodates legal and letter size hanging file folders

EXTERIOR FEATURES:



- Seamless design provides a sleek, attractive high-end appearance
- Easy-to-use recessed handles with label holders

Dimensions (H x W x D)	Capacity	Ship. Weight
Exterior 27.6" x 19.6" x 31" 70.1 cm x 49.8 cm x 78.7 cm	4.7 cu. ft. 132 liters	280 lbs. 127 kg
Drawer Interior 10.3" x 15.1" x 26" 26.2 cm x 38.4 cm x 66.0 cm		

USA MADE UNSURPASSED PROTECTIVE STORAGE SINCE 1930

DIMENSIONAL ILLUSTRATIONS

FRONT VIEW



SIDE VIEW