

SPEAKMAN®

SEF-1000

EYESAVER®

FAUCET

DEscription

the SEF-1000 Eyesaver® faucet model allows a customer to convert their existing Speakman widespread faucet into a Speakman SEF-1800 Eyesaver® faucet. The SEF-1800 combines a gooseneck faucet with an independently operated eyewash. Lead free brass construction.

SpEcificationS

Operation: Pull handle to operate the eyewash

Supply: Eyewash connection- 1/2" NPT male
Faucet Gooseneck - inlets through the adapter tee have 3/8" male connections (SEF-1000 comes standard with 3/8" compression hoses to connect to Speakman widespread valves.

Widespread Valves: Not included

Finish: Chrome plated brass

Eyewash Activation: Pull handle with graphics

Eyewash Sprays: Aerated sprays

Eyewash Flow Rate: 2.4 GPM at 30 psi. flowing

Counter Thickness: Up to 2" thick

Pressure: 30 psi. minimum flow pressure, 125 psi. maximum static pressure

Compatability: Connects to any Speakman widespread faucet with flexible hose connections. Connects to any competitor widespread faucet that can connect to 3/8" compression fittings via flexible hose. (hardware not supplied)

Approvals: Meets ASME A112.18.1, ANSI Z358.1, CSA B125-98 and CA AB1953

Vacuum Breaker (ST option): Approved by ASSE, UPC and CSA. Meets the ANSI/ASSE 1035 standard for "Laboratory Faucet Vacuum Breakers", CSA B64.8 and UPC.

Shipping Weight: 10 LBS.

options

- BO Vandal-resistant 0.5 gpm flow control
- ST* Serrated tip with vacuum breaker
- tW tepid water supply
- FP* Foot pedal activation of faucet
- LF 2.2 gpm laminar flow control outlet
- 8 8" Gooseneck spread
- NA Non-aerated spray heads

