

IP Camera Comparison Chart												
Model	Indoor / Outdoor	Type	PoE / Type	Lens	IR LED Range	Max. Resolution	WDR	SD Card Slot	2-Way Audio	Voltage	Streams	ONVIF Profile S
O2D10	Outdoor	Dome	Yes, af	3-9mm VF motorized	65'	1920x1080 @ 60fps	Yes	Yes	Yes	12VDC	4	Yes
O2D4	Outdoor	Dome	Yes, af	3.6-16mm VF	49'	1920x1080 @ 30fps	Yes	Yes	Yes	12VDC	5	Yes
O5MDP1	Outdoor	Mini-Dome	Yes, af	0.98-1.12mm panomorph	N/A	2592x1944 @ 10fps	Yes	Yes	Yes	12VDC	5	Yes
OiD4	Outdoor	Dome	Yes, af	3.6-16mm VF	Intensifier®	1080x720 @ 60fps	Yes	Yes	Yes	12VDC	5	Yes
OiMD1	Outdoor	Mini-Dome	Yes, af	3.7mm fixed	Intensifier®	1080x720 @ 60fps	Yes	Yes	Yes	12VDC	5	Yes
O2MD1	Outdoor	Mini-Dome	Yes, af	3.7mm fixed	30'	1920x1080 @ 30fps	Yes	Yes	Yes	12VDC	5	Yes
O2MD2	Outdoor	Mini-Dome	Yes, af	3.7mm fixed	30'	1920x1080 @ 30fps	Yes	No	No	12VDC	3	Yes
VIP3D2M	Outdoor	Dome	Yes, af	3-9mm VF motorized	65'	2048x1536 @ 20fps	Yes	Yes	Yes	Dual	3	Yes
VIP2D2M	Outdoor	Dome	Yes, af	3-9mm VF motorized	65'	1920x1080 @ 30fps	No	Yes	Yes	Dual	3	Yes
VIP2D2	Outdoor	Dome	Yes, af	3-9mm VF	N/A	1920x1080 @ 30fps	No	Yes	Yes	Dual	3	Yes
O2B16	Outdoor	Bullet	Yes, af	3-9mm VF motorized	98'	1920x1080 @ 60fps	Yes	Yes	Yes	Dual	4	Yes
O2B2	Outdoor	Bullet	Yes, af	3.6-16mm VF	90'	1920x1080 @ 30fps	Yes	Yes	Yes	12VDC	5	Yes
O2IR56B1	Outdoor	Bullet	Yes, af	2.8-10mm VF	90'	1920x1080 @ 30fps	Yes	Yes	Yes	12VDC	5	Yes
VIP2B1M	Outdoor	Bullet	Yes, af	3-9mm VF motorized	80'	1920x1080 @ 30fps	No	Yes	No	12VDC	3	Yes
O2B5	Outdoor	Bullet	Yes, af	3.7mm fixed	82'	1920x1080 @ 30fps	Yes	Yes	Yes	12VDC	5	Yes
VIP2B3	Outdoor	Bullet	Yes, af	3.7mm fixed	65'	1920x1080 @ 30fps	No	Yes	No	Dual	3	Yes
O2MB1	Outdoor	Mini-Bullet	Yes, af	3.7mm fixed	N/A	1920x1080 @ 30fps	Yes	Yes	Yes	12VDC	5	Yes
O2MT61	Outdoor	Mini-Turret	Yes, af	3.7mm fixed	N/A	1920x1080 @ 30fps	Yes	Yes	Yes	12VDC	5	Yes
OINT56B1G	Outdoor	Bullet	No	2.8-12mm VF	N/A	704x480 @ 30fps	No	No	Yes	12VDC	5	Yes
OINT03D1G	Outdoor	Turret	No	2.8-12mm VF	N/A	704x480 @ 30fps	No	No	Yes	12VDC	5	Yes
O2P30	Outdoor	PTZ	Yes, at	4.3-129mm, 30x optical zoom	N/A	1920x1080 @ 30fps	Yes	Yes	Yes	24VAC	2	Yes
O2PTZ22D5W	Outdoor	PTZ	Yes, at	4.7-94mm, 20x optical zoom	N/A	1920x1080 @ 30fps	No	Yes	Yes	12VDC	5	Yes
VIP2PTZ12X	Outdoor	PTZ	Yes, af	5.32-62.61mm, 12x optical zoom	N/A	1920x1080 @ 60fps	Yes	No	Yes	Dual	3	Yes
OPTZ36XO	Outdoor	PTZ	Yes, at	3.4-122.4mm, 36x optical zoom	N/A	704x480 @ 30fps	No	Yes	Yes	12VDC	5	Yes
OPTZ33D5W	Outdoor	PTZ	No	3.94-46.05mm, 12x optical zoom	N/A	704x480 @ 30fps	No	No	Yes	12VDC	5	Yes
O2DP14	Indoor	Dome	Yes, af	3-9mm VF motorized	65'	1920x1080 @ 60fps	Yes	Yes	Yes	12VDC	4	Yes
O2DP8	Indoor	Dome	Yes, af	3.6-16mm VF	49'	1920x1080 @ 30fps	Yes	Yes	Yes	12VDC	5	Yes
VIP2D1M	Indoor	Dome	Yes, af	3-9mm VF motorized	N/A	1920x1080 @ 30fps	No	Yes	No	12VDC	3	Yes
VIP1D1	Indoor	Dome	Yes, af	3-9mm VF	N/A	1280x1024 @ 30fps	No	Yes	No	12VDC	3	Yes
O2DP9	Indoor	Mini-Dome	Yes, af	3.7mm fixed	30'	1920x1080 @ 30fps	Yes	No	No	12VDC	3	Yes
VIP2P1	Indoor	Mini-Dome	Yes, af	3.7mm fixed	N/A	1920x1080 @ 30fps	No	Yes	No	12VDC	3	Yes
VIP2P1N	Indoor	Mini-Dome	Yes, af	3.7mm fixed	N/A	1920x1080 @ 30fps	No	Yes	No	12VDC	3	Yes
O2PTZ34D5W	Indoor	PTZ	Yes, at	4.7-94mm, 20x optical zoom	N/A	1920x1080 @ 30fps	No	Yes	Yes	12VDC	5	Yes
OPTZ36XI	Indoor	PTZ	Yes, at	3.4-122.4mm, 36x optical zoom	N/A	704x480 @ 30fps	No	Yes	Yes	12VDC	5	Yes

IP Camera Comparison Chart

IP Camera Comparison Chart

Model	Indoor / Outdoor	Type	PoE / Type	Lens	IR LED Range	Max. Resolution	WDR	SD Card Slot	2-Way Audio	Voltage	Streams	ONVIF Profile S
O2T6	Indoor	Box	Yes, af	CS type	N/A	1920x1080 @ 30fps	Yes	Yes	Yes	12VDC	5	Yes
VIP2C1P	Indoor	Cube	Yes, af	2.6mm fixed	PIR/White LED	1600x1200 @ 15fps	No	Yes	Yes	5VDC	3	Yes
VIP2C1N	Indoor	Cube	No	2.6mm fixed	N/A	1600x1200 @ 15fps	No	Yes	No	5VDC	3	Yes
OS101	Indoor	Encoder	Yes, af	N/A	N/A	704x480 @ 30fps	No	Yes	Yes	12VDC	3	Yes
OS102	Indoor	Encoder	No	N/A	N/A	704x480 @ 30fps	No	No	No	12VDC	3	Yes
D1BD	Indoor	Encoder	No	N/A	N/A	704x480 @ 30fps	No	No	No	12VDC	3	Yes