

PRODUCT SPECIFICATION

Printed: 2/10/2014

Catalog : A1120

Ammonium Acetate, Crystal, Reagent, ACS

CAS# : 631-61-8

Formula : C₂H₇NO₂

Formula Weight : 77.08

Test

**Limit
Min. Max.**

Test	Limit Min. Max.
ASSAY	97 % --
pH OF A 5% SOLUTION @ 25[dC	6.7 - 7.3
INSOLUBLE MATTER	-- 0.005 %
RESIDUE AFTER IGNITION	-- 0.01 %
CHLORIDE (Cl)	-- 5 PPM
NITRATE (NO ₃)	-- 0.001 %
SULFATES (SO ₄)	-- 0.001 %
HEAVY METALS (as Pb)	-- 5 PPM
IRON (Fe)	-- 5 PPM
IDENTIFICATION	TO PASS TEST
RETEST DATE	