

PRODUCT SPECIFICATION

Printed: 2/10/2014

Catalog : A1220

Ammonium Oxalate, Monohydrate, Crystal, Reagent, ACS

CAS# : 6009-70-7

Formula : C₂H₈N₂O₄[H₂O

Formula Weight : 142.11

Test

Limit
Min. Max.

| ASSAY [(NH ₄) ₂ C] | | 99.0 - 101.0 % |
|---|--|----------------|
| INSOLUBLE MATTER | | -- 0.005 % |
| RESIDUE AFTER IGNITION | | -- 0.02 % |
| CHLORIDE (Cl) | | -- 0.002 % |
| SULFATES (SO ₄) | | -- 0.002 % |
| HEAVY METALS (as Pb) | | -- 5 PPM |
| IRON (Fe) | | -- 2 PPM |
| RETEST DATE | | |