

**PRODUCT SPECIFICATION**

**Printed:** 2/10/2014

**Catalog :** BE129

Benzethonium Chloride, USP

**CAS# :** 121-54-0

**Formula :** C<sub>27</sub>H<sub>42</sub>ClNO<sub>2</sub>

**Formula Weight :** 448.08

Test	Limit	
	Min.	Max.
ASSAY (DRIED BASIS)	97.0	103.0%
MELTING RANGE	158°	163°C
LOSS ON DRYING	--	5.0%
RESIDUE ON IGNITION	--	0.1%
AMMONIUM COMPOUNDS	--	TO PASS TEST
IDENTIFICATION	--	TO PASS TEST
RETEST DATE		
RESIDUAL SOLVENTS		TO PASS TEST