

PRODUCT SPECIFICATION

Printed: 2/10/2014

Page 1 of 1

Catalog : BE156

Hydrous Benzoyl Peroxide, USP

CAS# : 94-36-0

Formula : C₁₄H₁₀O₄

Formula Weight : 242.23

Test

Limit Min. Max.

Test	Limit Min. Max.
ASSAY (C ₁₄ H ₁₀ O ₄)	65.0 - 82.0 %
CHROMATOGRAPHIC PURITY	--TO PASS TEST
RESIDUAL SOLVENTS	--TO PASS TEST
IDENTIFICATION	--TO PASS TEST
RETEST DATE	