

**PRODUCT SPECIFICATION**

**Printed:** 2/10/2014

Page 1 of 1

**Catalog :** B1068

Benzalkonium Chloride Solution, 50 Percent, NF

**CAS# :**

Test	Limit	
	Min.	Max.
ASSAY	47.5 - 52.5 %	
RATIO OF ALKYL COMPONENTS	TO PASS TEST	
LIMITS OF AMINES AND AMINE SALTS	TO PASS TEST	
ALCOHOL CONTENT	-- 10 %	
ACIDITY OR ALKALINITY	TO PASS TEST	
LIMIT OF BENZYL ALCOHOL	-- 0.5 %	
LIMIT OF BENZYL BENZALDEHYDE	-- 0.15 %	
LIMIT OF (CHLOROMETHYL) BENZENE	-- 0.05 %	
IDENTIFICATION	--TO PASS TEST	
RESIDUAL SOLVENTS	--TO PASS TEST	
RETEST DATE		