

PRODUCT SPECIFICATION

Printed: 2/10/2014

Page 1 of 1

Catalog : CA192

Carboxymethylcellulose Sodium, Medium Viscosity, Viscosity of 2 Percent Aqueous Solution @ 25 DEG C: 400-800 cP, USP

CAS# : 9004-32-4

Test	Limit	
	Min.	Max.
SODIUM (DRIED BASIS)	6.5 - 9.5%	
pH OF A 1 % SOLUTION @ 25[dC	6.5 - 8.5	
LOSS ON DRYING	--	10.0%
HEAVY METALS	--	0.002%
VISCOSITY OF 2% AQUEOUS SOLN. @25 C	400 - 800 CPS	
IDENTIFICATION	TO PASS TEST	
EXPIRATION DATE		
RESIDUAL SOLVENTS	TO PASS TEST	