

PRODUCT SPECIFICATION

Printed: 2/10/2014

Page 1 of 1

Catalog : CA194

Carboxymethylcellulose Sodium, High Viscosity, Viscosity of 1 Percent Aqueous Solution @ 25 DEG C: 1500-3000 cP, USP

CAS# : 9004-32-4

Test

**Limit
Min. Max.**

	Limit
	Min. Max.
SODIUM (DRIED BASIS)	6.5 - 9.5%
pH OF A 1 % SOLUTION @ 25[dC	6.5 - 8.5
LOSS ON DRYING	-- 10.0%
HEAVY METALS	-- 0.002%
VISCOSITY OF 1% AQUEOUS SOLUTION @25[dC	1,500 - 3,000 cps
IDENTIFICATION	TO PASS TEST
RETEST DATE	
RESIDUAL SOLVENTS	TO PASS TEST