

PRODUCT SPECIFICATION

Printed: 2/10/2014

Catalog : CA185

Camphor, Synthetic, USP

CAS# : 76-22-2

Formula : C10H16O

Formula Weight : 152.23

Test

**Limit
Min. Max.**

MELTING RANGE	174° - 179°C
SPECIFIC ROTATION	OPTICALLY INACTIVE
APPEARANCE OF SOLUTION	--TO PASS TEST
NONVOLATILE RESIDUE	-- 0.05%
HALOGENS	-- 0.035%
IDENTIFICATION	--TO PASS TEST
EXPIRATION DATE	
RESIDUAL SOLVENTS	TO PASS TEST