

PRODUCT SPECIFICATION

Printed: 2/10/2014

Catalog : ED150

Edetate Disodium, Dihydrate, USP

CAS# : 6381-92-6

Formula : C₁₀H₁₄N₂Na₂O₈[2H₂O

Formula Weight : 372.24

Test

Limit
Min. Max.

Test	Limit
	Min. Max.
ASSAY (DRIED BASIS)	99.0 - 101.0 %
pH OF A 5% SOLUTION @ 25[dC	4.0 - 6.0
LOSS ON DRYING	8.7 - 11.4 %
CALCIUM (Ca)	--TO PASS TEST
HEAVY METALS	-- 0.005 %
NITRILOTRIACETIC ACID[n[(HOCOCH ₂) ₃ N]	--TO PASS TEST
IDENTIFICATION	--TO PASS TEST
EXPIRATION DATE	
RESIDUAL SOLVENTS	--TO PASS TEST