

PRODUCT SPECIFICATION

Printed: 2/10/2014

Catalog : E1001

Disodium EDTA, Dihydrate, FCC

CAS# : 6381-92-6

Formula : C₁₀H₁₄N₂Na₂O₈[2H₂O

Formula Weight : 372.24

Test

Limit
Min. Max.

| ASSAY (C ₁₀ H ₁₄ O ₈ N ₂ Na ₂ 2H ₂ O) | 99.0 - 101.0 % |
|---|----------------|
| pH OF A 1 IN 100 SOLUTION | 4.3 - 4.7 |
| CALCIUM (Ca) | --TO PASS TEST |
| LEAD (Pb) | -- 10 MG/KG |
| NITRILOTRIACETIC ACID[n[(HOCOCH ₂) ₃ N] | --TO PASS TEST |
| IDENTIFICATION | --TO PASS TEST |
| EXPIRATION DATE | |