

PRODUCT SPECIFICATION

Printed: 2/10/2014

Catalog : L1040

Lead Acetate, Trihydrate, Crystal, Reagent, ACS

CAS# : 6080-56-4

Formula : C₄H₆O₄Pb[3H₂O

Formula Weight : 379.34

Test

Limit
Min. Max.

Test	Limit
	Min. Max.
ASSAY [Pb(CH ₃ COO) ₂ .3H	99.0 - 103.0 %
INSOLUBLE MATTER	-- 0.01 %
CHLORIDE (Cl)	-- 5 PPM
NITRATE AND NITRITE (asNO ₃)	-- 0.005 %
COPPER (Cu)	-- 0.002 %
IRON (Fe)	-- 0.001 %
SODIUM (Na)	-- 0.01 %
POTASSIUM (K)	-- 0.005 %
CALCIUM (Ca)	-- 0.005 %
RETEST DATE	