

PRODUCT SPECIFICATION

Printed: 2/10/2014

Page 1 of 1

Catalog : ME137

Methylcellulose, 4,000 cP, USP

CAS# : 9004-67-5

Test

Limit
Min. Max.

Test	Limit Min. Max.
ASSAY (asMETHOXYGROUPS,-OCH ₃)	26.0 - 33.0 %
APPARENT VISCOSITY OF A 2%(w/w)AQ. SOLN.@20C	TO PASS TEST
HEAVY METALS	-- 20 PPM
LOSS ON DRYING	-- 5.0 %
pH	-- 5.0 - 8.0
RESIDUE ON IGNITION	-- 1.5 %
IDENTIFICATION	--TO PASS TEST
RETEST DATE	
RESIDUAL SOLVENTS	--TO PASS TEST