

PRODUCT SPECIFICATION

Printed: 2/10/2014

Catalog : M1187

Methylparaben, FCC

CAS# : 99-76-3

Formula : C₈H₈O₃

Formula Weight : 152.15

Test

Limit
Min. Max.

Test	Limit
	Min. Max.
ASSAY (DRIED BASIS)	99.0 - 100.5 %
MELTING RANGE	125 - 128 C
ACIDITY	-- TO PASS TEST
LEAD (Pb)	-- 2 mg/kg
LOSS ON DRYING	-- 0.5 %
RESIDUE ON IGNITION	-- 0.05 %
IDENTIFICATION	-- TO PASS TEST
EXPIRATION DATE	