

PRODUCT SPECIFICATION

Printed: 2/10/2014

Catalog : PO158

Potassium Bicarbonate, Granular, USP

CAS# : 298-14-6

Formula : KHCO₃

Formula Weight : 100.12

Test

Limit
Min. Max.

	99.5 - 101.5 %
ASSAY (KHCO ₃)	99.5 - 101.5 %
LOSS ON DRYING (OVER SILICA)	-- 0.3 %
NORMAL CARBONATE	-- 2.5 %
HEAVY METALS (as Pb)	-- 0.001 %
RESIDUAL SOLVENTS	-- TO PASS TEST
IDENTIFICATION	-- TO PASS TEST
CERTIFIED KOSHER	