

PRODUCT SPECIFICATION

Printed: 2/10/2014

Catalog : PO200

Monobasic Potassium Phosphate, Crystal, NF

CAS# : 7778-77-0

Formula : KH₂PO₄

Formula Weight : 136.09

Test

**Limit
Min. Max.**

	Limit Min. Max.
ASSAY (KH ₂ PO ₄)	98.0 - 100.5 %
LOSS ON DRYING	-- 1.0 %
INSOLUBLE SUBSTANCES	-- 0.2 %
FLUORIDE	-- 0.001 %
ARSENIC (As)	-- 3 PPM
HEAVY METALS	-- 0.002 %
LEAD (Pb)	-- 5 PPM
IDENTIFICATION	-- TO PASS TEST
RETEST DATE	
RESIDUAL SOLVENTS	-- TO PASS TEST