

## PRODUCT SPECIFICATION

**Printed:** 2/10/2014

Page 1 of 1

**Catalog :** PR133

Propylparaben, NF, BP, EP

**CAS# :** 94-13-3

**Formula :** C<sub>10</sub>H<sub>12</sub>O<sub>3</sub>

**Formula Weight :** 180.20

Test	Limit	
	Min.	Max.
ASSAY	98.0 - 102.0 %	
MELTING RANGE	96° - 99°C	
COLOR OF SOLUTION	-- TO PASS TEST	
APPEARANCE OF SOLUTION	-- TO PASS TEST	
ACIDITY	-- TO PASS TEST	
RESIDUE ON IGNITION (SULPHATED ASH)	-- 0.10%	
RELATED SUBSTANCES	-- TO PASS TEST	
IDENTIFICATION	-- TO PASS TEST	
RETEST DATE		
RESIDUAL SOLVENTS	-- TO PASS TEST	