

## PRODUCT SPECIFICATION

**Printed:** 2/10/2014

**Catalog :** P1060

Phenol, Loose Crystal, Reagent, ACS

**CAS# :** 108-95-2

**Formula :** C<sub>6</sub>H<sub>6</sub>O

**Formula Weight :** 94.11

### Test

**Limit**  
**Min.    Max.**

Test	Limit
	Min.    Max.
ASSAY (C <sub>6</sub> H <sub>5</sub> OH)	99.0 %    --
FREEZING POINT (DRY)	40.5 C    --
CLARITY OF SOLUTION	TO PASS TEST
RESIDUE AFTER EVAPORATION	--    0.05 %
WATER	--    0.5 %