

PRODUCT SPECIFICATION

Printed: 2/10/2014

Catalog : P1192

Potassium Biphthalate, BiotechGrade

CAS# : 877-24-7

Formula : C₈H₅KO₄

Formula Weight : 204.22

Test	Limit	
	Min.	Max.
ASSAY (C ₈ H ₅ O ₄ K;DRIEDBASIS)	99.5 %	--
pH OF A 0.1M SOLUTION @ 20°C	3.5	5.0
INSOLUBLE MATTER	--	0.01 %
CHLORIDE	--	0.002 %
SULFATES	--	0.005 %
ALUMINUM	--	0.0005 %
CALCIUM	--	0.001 %
CADMIUM	--	0.0005 %
CHROMIUM	--	0.0005 %
COPPER	--	0.0005 %
IRON	--	0.0005 %
MAGNESIUM	--	0.0005 %
SODIUM	--	0.005 %
NICKEL	--	0.0005 %
LEAD	--	0.0005 %
ZINC	--	0.0005 %