

PRODUCT SPECIFICATION

Printed: 2/10/2014

Catalog : P1430

n-Propyl Alcohol, Reagent, ACS

CAS# : 71-23-8

Formula : C₃H₈O

Formula Weight : 60.10

Test

**Limit
Min. Max.**

| Test | Limit Min. Max. |
|-------------------------------|--------------------|
| ASSAY | 99.5 % -- |
| SOLUBILITY IN WATER | TO PASS TEST |
| COLOR (APHA) | -- 10 |
| RESIDUE AFTER EVAPORATION | -- 0.001 % |
| WATER | -- 0.2 % |
| TITRABLE ACID | -- 0.0004 meq/g |
| ETHYL ALCOHOL | -- 0.01 % |
| METHANOL (CH ₃ OH) | -- 0.01 % |
| ISOPROPYL ALCOHOL | -- 0.05 % |
| CARBONYL COMPOUNDS: | -- 0.03 % |
| IDENTIFICATION | TO PASS TEST |
| EXPIRATION DATE | |