

PRODUCT SPECIFICATION

Printed: 2/10/2014

Page 1 of 1

Catalog : SO138

Dibasic Sodium Phosphate, Dried, USP

CAS# : 7558-79-4

Formula : Na₂HPO₄

Formula Weight : 141.96

Test

Limit
Min. Max.

Test	Limit Min. Max.
ASSAY (DRIED BASIS)	98.0 - 100.5 %
LOSS ON DRYING	-- 5.0 %
INSOLUBLE SUBSTANCES	-- 0.4 %
CHLORIDE (Cl)	-- 0.06 %
SULFATES (SO ₄)	-- 0.2 %
ARSENIC (As)	-- 16 PPM
HEAVY METALS (as Pb)	-- 0.002 %
IDENTIFICATION	-- TO PASS TEST
EXPIRATION DATE	
RESIDUAL SOLVENTS	-- TO PASS TEST