

PRODUCT SPECIFICATION

Printed: 2/10/2014

Catalog : SO182

Sodium Metabisulfite, Granular, NF, EP, BP, JP

CAS# : 7681-57-4

Formula : Na₂S₂O₅

Formula Weight : 190.11

Test

**Limit
Min. Max.**

Test	Limit Min. Max.
ASSAY (SO ₂)	65.0 - 67.4%
ASSAY (Na ₂ S ₂ O ₅)	95.0 - 100.5%
pH OF A 5% SOLUTION	3.5 - 5.0
CHLORIDE (Cl)	-- 0.05%
IRON (Fe)	-- 20 PPM
THIOSULFATE (S ₂ O ₃)	TO PASS TEST
HEAVY METALS (as Pb)	-- 20 PPM
APPEARANCE OF SOLUTION	TO PASS TEST
ARSENIC (As)	-- 4 PPM
RESIDUAL SOLVENTS	TO PASS TEST
IDENTIFICATION	TO PASS TEST
EXPIRATION DATE	