

PRODUCT SPECIFICATION

Printed: 2/10/2014

Page 1 of 1

Catalog : ST110

Stearic Acid, Type 50, Powder, NF

CAS# : 57-11-4

Test	Limit	
	Min.	Max.
ASSAY: STEARIC ACID	40.0 - 60.0 %	
ASSAY: STEARIC ACID & PALMITIC ACID	90.0 %	--
FREEZING POINT	53 - 59 C --	
IODINE VALUE	--	4
RESIDUE AFTER IGNITION	--	0.1 %
HEAVY METALS	--	0.001 %
ACIDITY	TO PASS TEST	
COLOR OF SOLUTION	TO PASS TEST	
IDENTIFICATION	TO PASS TEST	
EXPIRATION DATE		
RESIDUAL SOLVENTS	TO PASS TEST	