PRODUCT SPECIFICATION

Printed: 2/10/2014

Catalog : S1300 Sodium Hydroxide, Low Chloride, Pellets, Reagent Special, ACS

CAS# : 1310-73-2

Formula : NaOH

Formula Weight : 40.00

Test	Limit Min.	Limit Max.
ASSAY (NaOH)	98.0 %	--
SODIUM CARBONATE (Na_2CO_3)	--	0.5 %
CHLORIDE (Cl)	--	0.005 %
NITROGEN COMPOUNDS (as N)	--	0.001 %
PHOSPHATE (PO_4)	--	0.001 %
SULFATE	--	0.003 %
HEAVY METALS (as Ag)	--	0.002 %
IRON (Fe)	--	0.001 %
MERCURY	--	0.1 PPM
NICKEL (Ni)	--	0.001 %
CALCIUM (Ca)	--	0.005 %
MAGNESIUM (Mg)	--	0.002 %
POTASSIUM (K)	--	0.02 %
EXPIRATION DATE		